



© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: MAPLGA, THIN PROFILE, 8 X 8 X 0.91 PKG, 0.5 MM PITCH, 63 I/O	DOCUMENT NO: 98ASA00393D	REV: B
	STANDARD: NON-JEDEC	
	SOT1647-1	08 JAN 2016



DETAIL E
VIEW ROTATED 90° CW



BOTTOM VIEW

© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE
TITLE: MAPLGA, THIN PROFILE, 8 X 8 X 0.91 PKG, 0.5 MM PITCH, 63 I/O	DOCUMENT NO: 98ASA00393D	REV: B
	STANDARD: NON-JEDEC	
	SOT1647-1	08 JAN 2016



NOTES:

- 1. ALL DIMENSIONS IN MILLIMETERS.
- 2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.

3. DIMENSION APPLIES TO ALL LEADS AND FLAG AREAS.

4. PARALLELISM MEASUREMENT SHALL EXCLUDE ANY EFFECT OF MARK ON TOP SURFACE OF PACKAGE.

© NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE	PRINT VERSION NOT TO SCALE	
TITLE: MAPLGA, THIN PROFILE, 8 X 8 X 0.91 PKG, 0.5 MM PITCH, 63 I/O		DOCUMENT NO: 98ASA00393D	REV: B
		STANDARD: NON-JEDEC	
		SOT1647-1	08 JAN 2016