



TJA1410, 10BASE-T1S PMD Transceiver

TJA1410

Preproduction


This page contains information on a preproduction product. Specifications and information herein are subject to change without notice. For additional information [contact support](#) or your sales representative.

Last Updated: Apr 4, 2024

TJA1410 is NXP's 10BASE-T1S OA TC14 specification-compliant PMD transceiver. It communicates over the OA 3-pin interface with the host MCU or switch, which must have the 10BASE-T1S digital PHY incorporated. The device comes in our compact HVSON8 (3 mm x 3 mm) package. The transceiver is made in our high-voltage process technology to guarantee best-in-class EMC performance.

The TJA1410 complies with all OA TC14 conformance test specifications and is designed according to ISO 26262 to meet ASIL B functional safety requirements. It also supports topology discovery as an advanced diagnostics feature. Further, it fully supports OPEN Alliance TC14-TC10 remote wake-up over the Ethernet data line.

10BASE-T1S PMD Transceiver Block Diagram



View additional information for [TJA1410, 10BASE-T1S PMD Transceiver](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.