

NXP®
NTAG 5 link

NTAG® 5 link: NFC Forum Compliant I²C Bridge

Targeted to sensor-driven applications, this highly integrated NFC tag creates a secure, standard-based link from the device to the cloud to address and even power sensors.



IoT on demand

Supply, read out, and send sensor data to the cloud, without an MCU



Smart Living

Install and maintain a smart home network with just a tap



Industrial

Use a long-range reader to calibrate and parameterize at the end of production

KEY BENEFITS

- ▶ Reading distance with long-range reader >60 cm (>25 inches)
- ▶ Zero-power readout of an I²C sensor
- ▶ Energy-efficient design with reduced bill of material
- ▶ Flexible split between three open and/or protected memory areas
- ▶ Adjustable security level up to AES mutual authentication
- ▶ Interoperable data exchange (NFC Forum compliant)
- ▶ 2048 bytes user memory, 256 bytes SRAM
- ▶ Configurable wired interfaces: I²C master and slave, PWM, GPIO, NFC field detection
- ▶ Energy harvesting with configurable output up to 30 mW
- ▶ Scalable security: 32-/64-bit password protection, 3 configurable user memory areas, ECC-based reprogrammable originality signature, 128-bit-AES mutual authentication
- ▶ NFC silence to disable NFC interface

KEY FEATURES

- ▶ NFC Forum compliant Type 5 tag
- ▶ ISO/IEC 15693 compliant

nfc everywhere



- ▶ Low-power consumption: <6 μA standby, <0.25 μA hard power-down
- ▶ Wide temp range: -40 to +85 $^{\circ}\text{C}$

NXP's NTAG 5 link lets designers of sensor-equipped systems add an NFC interface with a wired host interface that's configurable as an I²C master/slave, a pulse width modulator (PWM), or a general-purpose I/O (GPIO). Operating at 13.56 MHz, it is an NFC Forum compliant contactless tag that can be read and written by an NFC-enabled device at close range and by an ISO/IEC 15693-enabled industrial reader over a longer range.

DIRECT SENSOR CONNECTION

The NTAG 5 link can act as a direct bridge between an NFC-enabled device and any I²C slave, such as a sensor or external memory. This is especially useful in environments that require zero-power, single-shot measurements.

CLOUD CONNECTIVITY

With NTAG 5 link, the device can connect to the cloud with a single tap. The connection uses an NFC Forum compliant data exchange mechanism involving SRAM to ensure highly interoperable data transfers.

READ RANGE DUALITY

Support for ISO/IEC 15693 lets the NTAG 5 link communicate securely in two ways—with powerful industrial readers, at a range of up to 60 cm and with NFC-enabled devices (proximity range). This duality makes it possible for the device to be calibrated and parameterized automatically while in the factory and then, when put to use in the field, safely communicate with contactless devices such as smartphones.

INDEPENDENTLY PROTECTED MEMORY AREAS

The tag's 2048 bytes of memory can be divided into three areas, and each area can use a different protection level, varying from no protection to 32-/64-bit, password-protected read/write access or up to 128-bit-AES protected read/write access with mutual authentication. Different parties in the value chain can have their own dedicated memory areas for data storage.

The NTAG 5 link comes with pre-programmed proof-of-origin functionality to verify authenticity. The reprogrammable elliptic curve cryptography (ECC) originality signature can be locked or reprogrammed by the customer.

ENERGY HARVESTING

The NTAG 5 link can operate without a battery, by drawing power from the NFC reader instead. The tag supports energy harvesting, which means it can be used to supply power to other components in the system. When sufficient energy is available, the tag can supply a fixed, configurable voltage level to ensure a stable overall system.

NTAG 5 FAMILY SELECTION GUIDE

| | | NTAG 5 switch | NTAG 5 link | NTAG 5 boost | |
|-----------------------|---|--------------------------|--------------------------|--------------------------|-----|
| Contactless Interface | Pure passive ISO/IEC 15693 | yes | yes | yes | |
| | Active load modulation | no | no | yes | |
| Wired Interfaces | PWM | yes | yes | yes | |
| | GPIO | yes | yes | yes | |
| | I ² C | Slave | no | yes | yes |
| | | Transparent master | no | yes* | yes |
| Power | Energy harvesting with regulated V _{OUT} | yes, up to 30mW | yes, up to 30mW | only for passive | |
| | Stand-by current typical at RT | <6 μA @ RT | <6 μA @ RT | <10 μA @ RT | |
| | Hard power down current typical at RT | <0.25 μA @ RT | <0.25 μA @ RT | <0.25 μA @ RT | |
| Security | 32-/64-bit password | yes | yes | yes | |
| | 128-bit AES mutual authentication | no | yes* | yes | |
| | Reprogrammable ECC originality signature | yes | yes | yes | |

*not available for NTP5312

NTAG 5 LINK ORDERING INFORMATION

| Product Type ID | 12NC | Package | Packing | MOQ |
|--|----------------|---------|----------|---------|
| NTP53121G0JUA* • Bare die on wafer | 9353 582 08005 | FFC | Wafer | 1 Wafer |
| NTP53321G0JUA | 9353 582 09005 | | | |
| NTP53121G0JT* • 3.6 × 6.2 × 1.35 mm, no energy harv., hard power down | 9353 549 05431 | SO8 | Reel 13" | 2500 |
| NTP53321G0JT | 9353 549 11431 | TSSOP16 | Reel 13" | 2500 |
| NTP53121G0JTT* • 4.4 × 5.0 × 1.1 mm | 9353 624 11431 | | | |
| NTP53321G0JTT | 9353 624 96431 | | | |
| NTP53121G0JHK* • 1.8 × 2.6 × 0.5 mm | 9353 549 03115 | XQFN16 | Reel 7" | 4000 |
| NTP53321G0JHK | 9353 549 09471 | | | |

*no AES/I²C master functionality

www.nxp.com

NXP, the NXP logo, NTAG and the NTAG logo are registered trademarks of NXP B.V. All other product or service names are the property of their respective owners. © 2020 NXP B.V.

Date of release: July 2020
Document Number: NTAG5LINKFS REV 2

