

New Form Factor for Power Architecture® Technology in Industrial Applications

Nicholas Sargologos, John Ralston

Introduction

The Freescale Tower System is a set of feature-rich modular development solutions that support cost-effective rapid prototyping and simpler software migration. Tower boards are interchangeable and reusable modules that include open source design files to enable you to easily customize a design. The expansion of a

Tower System from a development tool into a development platform is simple and cost-effective. The Tower System helps you save months of development time—now and in the future—through rapid prototyping and tool re-use, and allows you to take advantage of our extensive Tower infrastructure with more than 50 Tower System modules or kits currently available.

Bringing Power Architecture® Technology to the Tower System

The most recent roadmap enhancement for the popular Tower System modular development platform introduced solutions based on the widely used Power Architecture® technology.

The strategy behind adding Power Architecture technology to our existing Tower platform was to leverage the ecosystem expansion capability of Tower infrastructure solutions and to provide our customers with a flexible design tool.

Figure 1: Freescale Tower System

Controller Module


- Tower MCU/MPU board
- Works stand-alone or in Tower System
- Features integrated debugging interface for easy programming and run control via standard USB cable

Secondary Elevator-

- Additional and secondary serial and expansion bus signals
- Standardized signal assignments
- Mounting holes and expansion connectors for side-mounting peripheral boards

Size

 Tower is approx. 3.5" H x 3.5" W x 3.5" D when fully assembled



Primary Elevator

- Common serial and expansion bus signals
- Two 2x80 connectors on backside for easy signal access and side-mounting board (LCD module)
- Power regulation circuitry
- Standardized signal assignments
- · Mounting holes

Board Connectors

- Four card-edge connectors
- Uses PCI Express[®] connectors (x16, 90 mm/3.5" long, 164 pins)

Peripheral Module

 Examples include serial interface module, memory expansion module and Wi-Fi[®] The newest modules in the Tower System series feature the cost-effective, highly versatile MPC8309 PowerQUICC communications processor and the multicore, high-performance QorlQ P1025 communications processor, which are ideal for robotics, factory automation, programmable logic controllers and industrial networking applications. The TWR-MPC8309 and TWR-P1025 controller modules along with the PX series of MCU Tower System modules bring Power Architecture technology to the Tower System.

Features and Benefits

The advanced Tower System modules, based on Power Architecture technology, are designed to deliver the richest feature sets yet offered in a Tower System form factor, with performance ranging from 130 to 2558 Dhrystone million instructions per second (DMIPS). A shared MQX™ real-time operating system (RTOS) and CodeWarrior integrated development environment (IDE) allow the Tower System platforms to easily facilitate customer application migration from MCUs to the more powerful Power Architecture MPUs with a rich variety of performance and connectivity options.

The Tower System Industrial Networking Development Platforms


At the heart of advanced Tower System modules based on Power Architecture technology are the highly versatile MPC8309 PowerQUICC II Pro communications processor and the multicore, high-performance QorlQ P1025 communications processor.

The MPC8309 features an e300c3 Power Architecture core with double precision floating point, 16 KB of instruction and data cache and up to 835 DMIPS (@417 MHz) of performance, while consuming less than 1.6 watts of power.

Table 1: Freescale Tower System: Features and Benefits

Features	Benefits				
Cost effective	Peripheral modules can be re-used with all Tower System controller modules, eliminating the need to purchase redundant hardware for future designs Enabling technologies such as LCD, serial and memory interfacing are offered off the shelf at a low cost to provide a customized enablement solution				
Modular and expandable	Processor/controller modules provide easy-to-use, reconfigurable hardware Interchangeable peripheral modules—serial, memory and graphical LCD—make customization easy Open-source hardware and standardized specifications promote the development of additional modules for added functionality and customization				
Speeds development time	Open source hardware and software allows quick development with proven designs On-board debug hardware for easy programming and debugging using only a standard USB cable				
Software enablement and support	Freescale, along with a strong alliance network, offers comprehensive solutions including development tools, debuggers, programmers and software				

Figure 2: TWR-MPC8309 Processor Module



The QorlQ P1 Tower module can be used stand-alone as a development board for various applications or as

a rapid-prototyping Tower System development platform. The dual-core

P1025 processor CPU cores run up to 533 MHz, and the device features a large L2 cache, DDR3 memory controller and Gigabit Ethernet support.



Both the MPC8309 and QorlQ P1025 feature an integrated QUICC Engine protocol offload processor, which can reduce BOM cost and design complexity by supporting industrial protocols such as PROFINET,

PROFIBUS, EtherNet/IP™ or EtherCAT® on-chip, instead of using an expensive external ASIC or FPGA. One more striking feature of both modules is that, in spite of the small form factor, they have the same functionality and

complexity of an MCU processor module, including SPI, RS232, IRQs, I²C, discrete flash and DDR2/DDR3 memory support, as seen in Figures 2, 3 and 4.

Figure 3: TWR-P1025 Processor Module





Figure 4: TWR-INDCTRL Industrial Control Expansion Peripheral Module



Coming in late 2012, the MPC8309 industrial development kit (TWR-MPC8309-KIT) will consist of three main components:

- The MPC8309 processor module (TWR-MPC8309, shown in Figure 2 above), measuring only 64 mm x 110 mm, supports comprehensive connectivity such as dual 10/100 Ethernet ports with IEEE® 1588 support, dual USB 2.0 connectors, twin RS-485 headers for PROFIBUS support, audio ports for headphone and microphone jacks, a mini-PCI connector and an SD card slot.
- The industrial applications peripheral module (TWR-INDCTRL, shown in Figure 3 above) provides a broad array of industrial interface ports, including four DB9 connectors for CAN protocol support, two SPI ports, an I²C port, an RS232 port and a third 10/100 Ethernet port.
- The Tower elevator module (TWR-ELEV) allows the TWR-MPC8309 main processor module to be connected to the industrial applications expansion card, as well as to other standard Tower peripheral modules.

An optional touch LCD daughter card (MPC830x-TLCD) features a 640 x 480 color LCD display with 12-key capacitive touch keypad. The TWR-MPC8309 main processor module can be used with the MPC830x-TLCD daughter card as a stand-alone single board computer (SBC) for applications such as programmable logic controllers (PLC), gateways and operator interface terminals. Combined with the industrial control expansion module in the conventional Tower System configuration, the TWR-MPC8309-KIT can support the development of robotics, test and measurement and other factory automation applications.

- The optional touch LCD daughter card (MPC830x-TLCD) features a 3.2" QVGA color LCD touchscreen with 12-key capacitive touch keypad. It can be attached directly to the TWR-MPC8309 main board in any configuration to support SBC functionality.
- The Tower serial card (TWR-SER) features a subset of the TWR-INDCTRL interfaces including one DB9 connector for CAN, one RS232 and a third 10/100 Ethernet port. It can be utilized to enable the full set of industrial connectivity supported by MPC8309 until TWR-INDCTRL becomes available.

Tower Board Infrastructure Based on Power Architecture Technology

Table 2 demonstrates the list of boards currently planned to be available on the Tower infrastructure based on the Power Architecture platform. It also gives the details of key features available with each of those boards and their primary targeted applications.

Advanced Tower System Modules Based on PX Series MCUs

Industrial market requirements for processing performance, safety and integration are rapidly increasing. The Freescale PX series of MCUs is designed for complex industrial control applications such as motion control, power generation, medical, aerospace and defense, motor drives, renewable energy conversion and robotics.

Based on the e200 Power Architecture core, the PX series MCUs offer singlecore performance up to 600 DMIPS, multicore options and up to 4 MB of embedded flash memory. A single MCU can control up to six motors, process complex math algorithms and manage more than the typical three communications connections at the same time. Its embedded safety architecture helps meet challenging industrial safety, reliability and environmental requirements with integrated features to simplify safety approvals for IEC 61511 and IEC 61508 (SIL3), FAA DO-178B Level A and FDA Class II to III. Advanced Tower System modules featuring the PX series of Power Architecture MCUs are planned for availability in early 2012.



Table 2: Examples of Boards in Tower Infrastructure Based on Power Architecture®

	TWR-PXD10	TWR-PXD20	TWR-PXN20	TWR-PXS20	TWR-PXS30	TWR-PXR40	TWR- MPC8309	TWR-P1025
Application	Industrial Display	Industrial Display	Industrial Gateways	Functional Safety	Functional Safety	Real-Time Applications: Motor Control	Industrial, Networking and Automation	Industrial, Networking and Automation
Flash/SRAM	1 MB/48 KB	2 MB/96 KB	2 MB/592 KB	1 MB/128 KB	2 MB/512 KB	4 MB/256 KB	Embedded 0 MB/0 MB	64 MB (NOR)
Board Flash/ DRAM							32 MB/128 MB	32 MB/128 ME
Code Warrior IDE	~	~	~	~	~	~	~	~
RAppID Dev Tool				V	V	V		
Motor Control				V	V		~	V
Debug Interface	JTAG/Nexus3 OSJTAG	JTAG/Nexus3 OSJTAG	JTAG/Nexus3 OSJTAG	JTAG/Nexus3 OSJTAG	JTAG/Nexus3 OSJTAG	JTAG/Nexus3 OSJTAG	JTAG/COP	JTAG/COP
Fault Correction				V	V			
Display	V	V					~	
Audio							~	
Potentiometer	V	V	V	V	V	V	~	
Accelerometer	~	V	V	V	V	~		V
Fieldbus							~	V
CAN	V	V	V	V	V	~	~	
UART			V	~	~	~	~	V
USB 2.0							~	V
Ethernet					V		~	V
PCI							~	V
SPI							~	V
ADC				V	V	V		
SD/SDIO							~	V
SPI Memory		V				V		V
TWRPI Socket		~		~	~			
eTPU						V		
IEEE® 1588							V	V
OS Support	MQXTM	MQX	MQX	MQX	MQX	MQX	MQX Linux® with RT Support GHS INTEGRITY QNX Neutrino	MQX Linux OS QNX Neutrino

Take Your Design to the Next Level

For a complete list of development kits and modules offered as part of the Freescale Tower System series based on Power Architecture technology, please visit **freescale.com/TowerPower**.

TowerGeeks.org is an online design engineer community that allows members to interact, develop designs and share ideas with the Tower System.



How to Reach Us:

Home Page:

freescale.com

Power Architecture Portfolio Information:

freescale.com/power

e-mail:

support@freescale.com

USA/Europe or Locations Not Listed:

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 1-800-521-6274 480-768-2130 support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064, Japan 0120 191014 +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd.
Technical Information Center
2 Dai King Street
Tai Po Industrial Estate,
Tai Po, N.T., Hong Kong
+800 2666 8080
support.asia@freescale.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright license granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

For more information, visit freescale.com/power

Freescale, the Freescale logo, CodeWarrior, PowerQUICC and QorlQ are trademarks of Freescale Semiconductor, Inc., Reg. U.S. Pat. & Tm. Off. The Power Architecture and Power.org word marks and the Power and Power.org logos and related marks are trademarks and service marks licensed by Power.org. All other product or service names are the property of their respective owners. © 2012 Freescale Semiconductor, Inc.

Document Number: PWRARBYNDBITSNFF REV 1



