


# MC9S12DT256

# **Target Applications**

- > Automotive applications
- > Industrial control

#### **Overview**

Freescale Semiconductor's HCS12 family of microcontrollers (MCUs) is the next generation of the highly successful 68HC12 architecture. Using Freescale's industry-leading 0.25 µs Flash, the MC9S12DT256 is part of a pin-compatible family that scales from 32 KB to 512 KB of Flash memory. The DT256 provides an upward migration path from Freescale's 68HC08, 68HC11 and 68HC12 architectures for applications that need larger memory, more peripherals and higher performance. Also, with the increasing number of CAN-based electronic control units (ECUs), its multiple network modules support this environment by enabling highly efficient communications between different network buses.



#### **Features Benefits** High-Performance 16-bit HCS12 CPU Core > Opcode compatible with the 68HC11 > 25 MHz bus operation at 5V for 40 ns minimum instruction cycle time and 68HC12 > C-optimized architecture produces extremely compact code **On-Chip Debug Interface** > Dedicated serial debug interface > Real-time in-circuit emulation and debug without expensive and cumbersome > On-chip breakpoints box emulators > Read/write memory and registers while running at full speed **Network Modules** > Three msCAN modules implementing the > Ability to link modules for higher buffer count CAN 2.0 A/B protocol > Programmable bit rate up to 1 Mbps • Five receive buffers per module with FIFO > FIFO receive approach superior for storage scheme event-driven networks • Three transmit buffers per module with internal prioritization **Integrated Third-Generation Flash Memory** > In-application reprogrammable > Flexibility to change code in the field > Self-timed, fast programming > Efficient end-of-line programming Fast Flash page erase—20 ms (512 bytes) > Total program time for 256 KB code is less than 10 seconds - Can program 16 bits in 20 μs while in burst mode Reduces production programming cost through ultra-fast programming > 5V Flash program/erase/read > No external high voltage or charge > Flash granularity—512 byte Flash erase/

# 4 KB Integrated EEPROM

2 byte Flash program

arrays

> Flexible protection scheme for protection against accidental program or erase

> Four independently programmable Flash

> Flexible block protection and security

- > EEPROM can be programmed in 46 μs
- > Can erase 4 bytes at a time and program 2 bytes at a time for calibration, security, personality and diagnostic information

> Virtual EEPROM implementation, Flash array

> Can erase one array while executing code

pump required

from another

usable for EE extension

### 10-bit Analog-to-Digital Converter (ADC)

- > Two, 8-channel ADCs
- > 7 μs, 10-bit single conversion time, scan mode available
- > Fast, easy conversion from analog inputs like temperature, pressure and fluid levels to digital values for CPU processing
- > Can effectively have 3.5 µs conversion time by sampling same signal with both ADCs





# **Benefits**

#### Clock Generation Module with Phase-Lock Loop (PLL)

- > Clock monitor with self clock mode in case of no external clock
- > Programmable clock frequency with 1024 options ranging from divide by 16 to multiply by 64 from base oscillator
- > Real-time interrupt
- > Watchdog

- > Reliable, robust operation
- > Provides high performance using low-cost reference crystals
- > Reduces generated noise
- > Reduces power consumption
- Easily able to implement real-time clock

## **Enhanced Capture Timer**

- > 8-channel, 16-bit with input capture, output compare and pulse accumulator
- > 16-bit modulus down counter
- > Flexible, programmable timer system

#### 8-bit or 16-bit Pulse-Width Modulation (PWM)

- > 8-channel, 8-bit or 4-channel, 16-bit PWM
- > PWM supports center-aligned operation
- > Efficiently implement motor control, battery charging or digital-to-analog (DAC) functions

#### **Two Serial Communications Interfaces**

> 8192 prescaler options

- > Asynchronous communication between the MCU and a terminal, computer or a network of MCUs
- > Exact baud rate matching

# **Three Serial Peripheral Interfaces**

> Up to 6.25 Mbps

> High-speed synchronous communication between multiple MCUs or between MCU and serial peripherals

#### Inter-IC (I2C) Bus

> 256 clock-rate options

- > Provides a simple, efficient method of data exchange between devices
- > Minimizes the need for large numbers of connections between devices and eliminates he need for an address decoder

# Up to 91 Input/Output (I/O) Lines

- > Programmable pull-ups/pull-downs
- > Dual drive capability

- > Reduce system cost
- > Able to tailor application for minimum EMC or high current loads

#### Application Notes and Engineering Bulletins

AN2206	Security and Protection on the HCS12 Family
AN2213	Using Cosmic Software's M68HC12 Compiler for MC9S12DP256
AN2216	MC9S12DP256 Software Development Using Metrowerks CodeWarrior™
AN2250	Audio Reproduction on HCS12 Microcontrollers
EB376	A comparison of the MC9S12DP256 (mask set 0K36N) versus the HC12
EB377	EB377Change Summary of the MC9S12DP256 mask set 0K79X versus 0K36N Engineering Brief
EB386	HCS12 D-Family Compatibility

#### **Data Sheets**

9S12DP256BDGV2 MC9S12DP256 Device Guide S12DP256PIMV2 MC9S12DP256 Port Integration

Module Block Guide

S12BDMV4 HCS12 Background Debug (BDM)

Block Guide

S12BKVD1 HCS12 Breakpoint (BKP) Block Guide S12CPUV2 HCS12 CPU Reference Manual S12MSCANV2 HCS12 Motorola Scalable Controller

Area Network Block Guide

S12ATD10B8CV2

HCS12 10-bit 8-channel Analog to Digital Block Guide

S12CRGV3 HCS12 Clock Reset Generator

Block Guide

S12ECT16B8CV1 HCS12 16-bit 8-channel Enhanced

Capture Timer Block Guide

HCS12 4K EEPROM Block Guide S12FFTS4KV2 S12FTS256KV2 HCS12 256K Flash Block Guide

S12IICV2 HCS12 I2C Block Guide

S12INTV1 HCS12 Interrupt (INT) Block Guide HCS12 Multiplexed External Bus S12MEBIV3 Interface (MEBI) Block Guide

S12MMCV4 HCS12 Module Mapping Control

(MMC) Block Guide S12PWM8B8CV1 HCS12 8-bit 8-channel Pulse-Width

Modulator Block Guide

**HCS12 Serial Communications** 

Interface Block Guide

HCS12 Serial Peripheral Interface Block Guide

HCS12 Voltage Regulator S12VREGV1

Block Guide

# Cost-Effective Development Tools

For more information on development tools, please refer to the Freescale Development Tool Selector Guide (SG1011).

M68KIT912DP256

S12SCIV2

S12SPIV2

\$495

Evaluation kit for development and evaluation of HCS12 application code that includes the M68EVB912DP256 and

**USBMULTILINKBDM** 

M68CYCLONEPRO

\$499

HC08/HCS08/HC12/HCS12 stand-alone Flash programmer or in-circuit emulator, debugger, Flash programmer; USB, serial or Ethernet interface options

USBMULTILINKBDM Universal HCS08/HCS12 in-circuit

\$99\*

emulator, debugger, and Flash programmer; USB PC interface

CWX-H12-SE

Free\*

CodeWarrior™ Special Edition for HCS12 MCUs; includes integrated development environment (IDE), linker, debugger, unlimited assembler, Processor Expert™ auto-code generator, full-chip simulation and limited C compiler

# Package Options

Part Number MC9S12DT256BCPV MC9S12DT256BVPV MC9S12DT256BMPV Package 112 LOFP 112 LQFP **112 LQFP** 

Temp. Range -40°C to +85°C -40°C to +105°C -40°C to +125°C



Learn More: For more information about Freescale products, please visit www.freescale.com.

