



BESS1500 Cell Monitoring Unit (CMU) with 3x 18S Capability

RDBESS774A3EVB **NEW**

Preproduction

This page contains information on a preproduction product. Specifications and information herein are subject to change without notice. For additional information [contact support](#) or your sales representative.

Last Updated: Jun 6, 2024

Available to selected customers only (non-disclosure agreement (NDA) required), please [contact support](#) or your local sales representative for more information.


The CMU3 - RDBESS774A3EVB is a battery cell monitoring unit (CMU) reference design with electrical transport protocol link (ETPL) communication interface towards a BMU. It is ideal for rapid prototyping of a high-voltage battery energy storage system (BESS) hardware and software. This board contains three MC33774A analog front ends (AFEs) in a daisy chain.

It can be used to monitor a battery module with up to 54 cells.

There are in total 27 GPIO/Analog measurement inputs for temperature or other measurements.

This board is part of the [RD-BESS1500BUN](#) reference design bundle.

CMU3 - RDBESS774A3EVB Block Diagram



View additional information for [BESS1500 Cell Monitoring Unit \(CMU\) with 3x 18S Capability](#).

Note: The information on this document is subject to change without notice.

www.nxp.com

NXP and the NXP logo are trademarks of NXP B.V. All other product or service names are the property of their respective owners. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. © 2024 NXP B.V.