



NOTES:  
 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.  
 2. CONTROLLING DIMENSION: INCH.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	1.840	1.880	46.74	47.75
B	1.840	1.880	46.74	47.75
C	0.110	0.140	2.79	3.56
D	0.016	0.020	0.41	0.51
G	0.100 BSC		2.54 BSC	
H	0.050 BSC		1.27 BSC	
K	0.150	0.170	3.81	4.32

**CASE 993A-01  
 ISSUE O**

**DATE 01/20/94**