

Test Report

號碼(No.): ETR23806224 日期(Date): 08-Sep-2023 頁數(Page): 1 of 4

MITSUBISHI MATERIALS CORPORATION 12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

以下測試樣品係由申請廠商所提供及確認 (The following sample(s) was/were submitted and identified by the applicant

as):

送樣廠商(Sample Submitted By) MITSUBISHI MATERIALS CORPORATION

樣品名稱(Sample Name) **SULA LIQUID**

SULA LIQUID-TS-TIN15,TS-TIN17,TS-TIN20,TS-TIN24 樣品型號(Style/Item No.)

收件日(Sample Receiving Date) 31-Aug-2023

測試期間(Testing Period) 31-Aug-2023 to 08-Sep-2023

測試需求(Test Requested) 依據客戶指定,參考RoHS 2011/65/EU Annex II及其修訂指令(EU) 2015/863測試

> DBP, BBP, DEHP, DIBP · (As specified by client, with reference to RoHS 2011/65/EU Annex II and amending Directive (EU) 2015/863 to determine

DBP, BBP, DEHP, DIBP contents in the submitted sample(s).)

測試結果(Test Results) 請參閱下一頁 (Please refer to following pages.)

結 論(Conclusion) 根據客戶所提供的樣品,其DBP, BBP, DEHP, DIBP的測試結果符合RoHS

2011/65/EU Annex II暨其修訂指令(EU) 2015/863之限值要求。 (Based on the performed tests on submitted sample(s), the test results of DBP, BBP, DEHP, DIBP comply with the limits as set by RoHS Directive (EU) 2015/863 amending

Annex II to Directive 2011/65/EU.)

Signed for and on behalf 💸 SĞS TAIWAN LTD. Chemical Laboratory - Taipei



CODE: D98824BB

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com.tw/terms-of-service and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at https://www.sgs.com.tw/terms-of-service. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.



Test Report

號碼(No.): ETR23806224 日期(Date): 08-Sep-2023 頁數(Page): 2 of 4

MITSUBISHI MATERIALS CORPORATION 12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

測試部位敘述 (Test Part Description)

No.1 : 透明液體 (TRANSPARENT LIQUID)

測試結果 (Test Results)

測試項目	測試方法	單位	MDL	結果	限值
(Test Items)	(Method)	(Unit)		(Result)	(Limit)
				No.1	
鄰苯二甲酸丁苯甲酯 (BBP) (Butyl benzyl		mg/kg	50	n.d.	1000
phthalate (BBP))					
鄰苯二甲酸二丁酯 (DBP) (Dibutyl	參考IEC 62321-8: 2017,以氣相層析儀/質	mg/kg	50	n.d.	1000
phthalate (DBP))	譜儀分析。(With reference to IEC 62321-				
鄰苯二甲酸二(2-乙基己基)酯 (DEHP) (Di-	8: 2017, analysis was performed by	mg/kg	50	n.d.	1000
(2-ethylhexyl) phthalate (DEHP))	GC/MS.)				
鄰苯二甲酸二異丁酯 (DIBP) (Diisobutyl		mg/kg	50	n.d.	1000
phthalate (DIBP))					

備註(Note):

- 1. mg/kg = ppm; 0.1wt% = 0.1% = 1000ppm
- 2. MDL = Method Detection Limit (方法偵測極限值)
- 3. n.d. = Not Detected (未檢出); 小於MDL / Less than MDL
- 4. 除非另有說明,參照ILAC-G8:09/2019,採用簡單二元(w=0)允收規則進行符合性判定;根據此規則,符合性結果之判定係以測試結果與限值做比較。(Unless otherwise stated, the decision rule for conformity reporting is based on Binary Statement for Simple Acceptance Rule (w=0) stated in ILAC-G8:09/2019. According to this rule, the judgement of conformity is based on the comparing test results with limits.)

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com.tw/terms-of-service. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.




Test Report

號碼(No.): ETR23806224 日期(Date): 08-Sep-2023

MITSUBISHI MATERIALS CORPORATION 12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

可塑劑分析流程圖 / Analytical flow chart - Phthalate

【測試方法/Test method: IEC 62321-8】



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com.tw/terms-of-service. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

頁數(Page): 3 of 4



Test Report

號碼(No.): ETR23806224

日期(Date): 08-Sep-2023

頁數(Page): 4 of 4

MITSUBISHI MATERIALS CORPORATION 12-6, TECHNO-PARK, SANDA, HYOGO 669-1339, JAPAN

* 照片中如有箭頭標示,則表示為實際檢測之樣品/部位. * (The tested sample / part is marked by an arrow if it's shown on the photo.)

ETR23806224



** 報告結尾 (End of Report) **

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com.tw/terms-of-service. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.