

Test Report 測試報告

Applicant: TA-I TECHNOLOGY CO., LTD.
申請廠商 大毅科技股份有限公司
No. 4, Ln. 17, Sec. 3, Nanshan Rd.,
Luzhu District, Taoyuan City 338,
Taiwan
桃園市蘆竹區南山路三段 17 巷 4 號

Number : TWNC01211361
報告號碼

Issue Date : Oct 04, 2023
報告發行日期

Sample Description 樣品敘述:

One (1) Group of Submitted Samples Said To Be :
以下測試樣品乃供應商所提供及確認:

Sample Description : END TERMINAL TARGET

樣品名稱

Style / Item No. : AZZ.003.0048

產品型號

Date Sample Received : Sep 23, 2023

收件日期


Date Test Started : Sep 23, 2023

開始測試日期

Test Conducted 測試執行:

As requested by the applicant, for details please refer to attached pages.
依申請商之要求, 細節請參考附頁.

Authorized By:
On behalf of Intertek Testing Services
Taiwan Limited



Matt Wang
General Manager



Signed by:



Thomas Chou
Manager



報告查詢 Report Verification



Test Conducted 測試內容 :

Test Result Summary 測試結果 :

Test Item 測試項目	Unit 單位	Test Method 測試方法	Result 結果	MDL
			Silvery metal	
Heavy Metal 重金屬				
Cadmium (Cd) Content 鎘含量	ppm	With reference to IEC 62321-5: 2013, by microwave or acid digestion and determined by ICP-OES. 參考 IEC 62321-5: 2013, 以微波或酸液消化法消化樣品並用感應耦合電漿原子發射光譜儀分析。	ND	2
Lead (Pb) Content 鉛含量	ppm	With reference to IEC 62321-5: 2013, by microwave or acid digestion and determined by ICP-OES. 參考 IEC 62321-5: 2013, 以微波或酸液消化法消化樣品並用感應耦合電漿原子發射光譜儀分析。	ND	2
Mercury (Hg) Content 汞含量	ppm	With reference to IEC 62321-4:2013+AMD1:2017, by microwave or acid digestion and determined by ICP-OES. 參考 IEC 62321-4:2013+AMD1:2017, 以微波或酸液消化法消化樣品並用感應耦合電漿原子發射光譜儀分析。	ND	2
Arsenic (As) Content 砷含量	ppm	With reference to USEPA 3052, by microwave digestion and determined by ICP-OES. 參考 USEPA 3052, 以微波消化法並用感應耦合電漿原子發射光譜儀分析。	ND	2
Beryllium (Be) Content 鈹含量	ppm	With reference to USEPA 3052, by microwave digestion and determined by ICP-OES. 參考 USEPA 3052, 以微波消化法並用感應耦合電漿原子發射光譜儀分析。	ND	2
Antimony (Sb) Content 銻含量	ppm	With reference to USEPA 3052, by microwave digestion and determined by ICP-OES. 參考 USEPA 3052, 以微波消化法並用感應耦合電漿原子發射光譜儀分析。	ND	2
Chromium VI (Cr(VI)) Content 六價鉻含量 @	µg/ cm ²	With reference to IEC 62321-7-1: 2015, by boiling water extraction and determined by UV-Vis Spectrophotometer or visual observation. 參考 IEC 62321-7-1: 2015, 以沸水萃取並用紫外光-可見光分光光度計分析或目測法判定。	Negative	0.10



Test Conducted 測試內容 :

Test Item 測試項目	Unit 單位	Test Method 測試方法	Result 結果	MDL
			Silvery metal	
Polybrominated Biphenyls (PBBs) 多溴聯苯				
Monobrominated Biphenyls (MonoBB) 單溴聯苯	ppm	With reference to IEC 62321-6: 2015, by solvent extraction and determined by GC-MS and further HPLC-DAD confirmation when necessary. 參考 IEC 62321-6: 2015, 以溶劑萃取並用氣相層析質譜儀分析, 必要時會以高效液相層析儀光二極體陣列偵測儀進行確認。	ND	5
Dibrominated Biphenyls (DiBB) 二溴聯苯	ppm		ND	5
Tribrominated Biphenyls (TriBB) 三溴聯苯	ppm		ND	5
Tetrabrominated Biphenyls (TetraBB) 四溴聯苯	ppm		ND	5
Pentabrominated Biphenyls (PentaBB) 五溴聯苯	ppm		ND	5
Hexabrominated Biphenyls (HexaBB) 六溴聯苯	ppm		ND	5
Heptabrominated Biphenyls (HeptaBB) 七溴聯苯	ppm		ND	5
Octabrominated Biphenyls (OctaBB) 八溴聯苯	ppm		ND	5
Nonabrominated Biphenyls (NonaBB) 九溴聯苯	ppm		ND	5
Decabrominated Biphenyl (DecaBB) 十溴聯苯	ppm		ND	5
Polybrominated Diphenyl Ethers (PBDEs) 多溴聯苯醚				
Monobrominated Diphenyl Ethers (MonoBDE) 單溴聯苯醚	ppm	With reference to IEC 62321-6: 2015, by solvent extraction and determined by GC-MS and further HPLC-DAD confirmation when necessary. 參考 IEC 62321-6: 2015, 以溶劑萃取並用氣相層析質譜儀分析, 必要時會以高效液相層析儀光二極體陣列偵測儀進行確認。	ND	5
Dibrominated Diphenyl Ethers (DiBDE) 二溴聯苯醚	ppm		ND	5
Tribrominated Diphenyl Ethers (TriBDE) 三溴聯苯醚	ppm		ND	5
Tetrabrominated Diphenyl Ethers (TetraBDE) 四溴聯苯醚	ppm		ND	5
Pentabrominated Diphenyl Ethers (PentaBDE) 五溴聯苯醚	ppm		ND	5
Hexabrominated Diphenyl Ethers (HexaBDE) 六溴聯苯醚	ppm		ND	5
Heptabrominated Diphenyl Ethers (HeptaBDE) 七溴聯苯醚	ppm		ND	5
Octabrominated Diphenyl Ethers (OctaBDE) 八溴聯苯醚	ppm		ND	5
Nonabrominated Diphenyl Ethers (NonaBDE) 九溴聯苯醚	ppm		ND	5
Decabrominated Diphenyl Ether (DecaBDE) 十溴聯苯醚	ppm		ND	5



Test Conducted 測試內容 :

Test Item 測試項目	Unit 單位	Test Method 測試方法	Result 結果	MDL
			Silvery metal	
Phthalates 鄰苯二甲酸酯				
Di(2-ethylhexyl) Phthalate (DEHP) 鄰苯二甲酸二(2-乙基己基)酯	ppm	With reference to IEC 62321-8:2017, by solvent extraction and determined by GC-MS. 參考 IEC 62321-8:2017, 以溶劑萃取並用氣相層析質譜儀分析。	ND	50
Dibutyl Phthalate (DBP) 鄰苯二甲酸二丁酯	ppm		ND	50
Benzyl Butyl Phthalate (BBP) 鄰苯二甲酸苯基丁酯	ppm		ND	50
Di-(Iso-Nonyl) Phthalate (DINP) 鄰苯二甲酸二異壬酯	ppm		ND	50
Di-(Iso-Decyl) Phthalate (DIDP) 鄰苯二甲酸二異癸酯	ppm		ND	50
Di-(N-Octyl) Phthalate (DNOP) 鄰苯二甲酸二辛酯	ppm		ND	50
Diisobutyl Phthalate (DIBP) 鄰苯二甲酸二異丁酯	ppm		ND	50
Di-n-pentyl phthalate (DPP, DnPP) 鄰苯二甲酸二戊酯	ppm		ND	50
Di-n-hexyl phthalate (DnHP) 鄰苯二甲酸二正己酯(二己酯)	ppm		ND	50
Bis(2-Methoxyethyl) phthalate (DMEP) 鄰苯二甲酸二(2-乙基甲醚)酯	ppm		ND	50
Halogen Content 鹵素含量				
Fluorine (F) 氟	ppm	With reference to EN 14582:2016 by combustion bomb with oxygen and determined by Ion Chromatography. 參考 EN 14582:2016, 以氧彈燃燒集氣法並用離子層析儀分析。	ND	50
Chlorine (Cl) 氯	ppm		ND	50
Bromine (Br) 溴	ppm		ND	50
Iodine (I) 碘	ppm		ND	50



Test Conducted 測試內容 :

Test Item 測試項目	Unit 單位	Test Method 測試方法	Result 結果	MDL
			Silvery metal	
Others 其他				
Medium Chain Chlorinated Paraffins (C14~C17) 中鏈氯化石蠟	ppm	With reference to ISO 18219, by solvent extraction and determined by GC-ECNI-MS. 參考 ISO 18219, 以溶劑萃取並用氣相層析-化學游離質譜儀分析。	ND	5
Bisphenol-A 雙酚-A	ppm	By solvent extraction and determined by LC-MS-MS. 以溶劑萃取並用液相層析串聯質譜儀分析。	ND	0.1
Hexabromocyclododecane (HBCDD) 六溴環十二烷	ppm	With reference to USEPA 3540C, by solvent extraction and determined by GC-MS. 參考 USEPA 3540C, 以溶劑萃取並用氣相層析質譜儀分析。	ND	10
Perfluorooctane Sulfonates Including PFOS, PFOSA, N-Me-FOSA, N-Et-FOSA, N-Me-FOSE, N-Et-FOSE 全氟辛磺酸含 PFOS, PFOSA, N-Me-FOSA, N-Et-FOSA, N-Me-FOSE, N-Et-FOSE	ppm	With reference to CEN/TS 15968:2010, by solvent extraction and determined by LC-MS-MS. 參考 CEN/TS 15968:2010, 以溶劑萃取並用液相層析串聯質譜儀分析。	ND	0.01
Perfluorooctanoic Acid (PFOA) 全氟辛酸	ppm	With reference to CEN/TS 15968:2010, by solvent extraction and determined by LC-MS-MS. 參考 CEN/TS 15968:2010, 以溶劑萃取並用液相層析串聯質譜儀分析。	ND	0.01
Tetrabromo bisphenol A (TBBPA) 四溴雙酚-A	ppm	With reference to USEPA 3540C, by solvent extraction and determined by GC-MS. 參考 USEPA 3540C, 以溶劑萃取並用氣相層析質譜儀分析。	ND	20
Polyvinyl Chloride (PVC) 聚氯乙烯	NA	By Beilstein's test (Flame Test) and FT-IR analysis. 以火焰法及傅立葉轉換紅外線光譜儀檢測。	Negative	NA

Remarks: ppm = Parts per million based on weight of tested sample = mg/kg
備註 百萬分之一, 依據測試樣品重量計算 = 毫克/公斤

ND = Not detected 未檢測出

MDL = Quantitation limit of test method 方法偵測極限

NA = Not applicable 不適用



Test Conducted 測試內容 :

@ The explanation of Chromium VI (Cr(VI)) analysis results 六價鉻分析結果說明

<u>Colorimetric result</u> 比色結果	<u>Qualitative Result</u> 定性結果	<u>Explanation</u> 說明
< 0.10 µg/cm ²	Negative 陰性	The result of sample is negative for Cr(VI). The sample coating is considered a non-Cr(VI) based coating. 六價鉻結果為陰性。樣品之鍍層可視為不含六價鉻。
≥ 0.10 µg/cm ² and ≤ 0.13 µg/cm ²	Inconclusive 不確定	The result of sample is considered to be inconclusive. If addition samples are available, recommend to add trials and get the average result for the final determination. 六價鉻結果為不確定。若可取得較多樣品，建議增加測試次數並取得其平均值，以評估最後結果。
> 0.13 µg/cm ²	Positive 陽性	The result of sample is positive for Cr(VI). The sample coating is considered to contain Cr(VI). 六價鉻結果為陽性。樣品之鍍層可視為含有六價鉻。 A result expresses as Positive, while not an actual value, which indicates a visual observation was used. 當結果以陽性表示，而非數值時，為使用目測法判定。

Responsibility of Chemist 分析人員 : Cloud Hsu / Vita Fu

Date Sample Received 樣品收件日期 : Sep 23, 2023

Test Period 樣品測試期間 : Sep 23, 2023 to Oct 02, 2023

RoHS Limit RoHS 限值

<u>Restricted Substances</u> 限用物質	<u>Limits</u> 限值
Cadmium (Cd) content 鎘含量	0.01% (100ppm)
Lead (Pb) content 鉛含量	0.1% (1000ppm)
Mercury (Hg) content 汞含量	0.1% (1000ppm)
Chromium VI (Cr(VI)) content 六價鉻含量	0.1% (1000ppm)
Polybrominated Biphenyls (PBBs) 多溴聯苯	0.1% (1000ppm)
Polybrominated Diphenyl Ethers (PBDEs) 多溴聯苯醚	0.1% (1000ppm)
Di(2-ethylhexyl) Phthalate (DEHP) 鄰苯二甲酸二(2-乙基己基)酯	0.1% (1000ppm)
Dibutyl Phthalate (DBP) 鄰苯二甲酸二丁酯	0.1% (1000ppm)
Benzyl Butyl Phthalate (BBP) 鄰苯二甲酸苯基丁酯	0.1% (1000ppm)
Diisobutyl Phthalate (DIBP) 鄰苯二甲酸二異丁酯	0.1% (1000ppm)

The limits were quoted from Annex II of 2011/65/EU and Amendment (EU) 2015/863 for homogeneous material.
本限值是依據歐盟指令 2011/65/EU 及其更新指令(EU) 2015/863 之附錄二針對均質材質所訂定。




Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:

Test for Cd/Pb/Hg/Chromium (VI)/PBBs/PBDEs Content RoHS 六項測試

Reference Method 參考方法 : Cd/Pb: IEC 62321-5:2013; Hg: IEC 62321-4:2013+AMD1:2017;
Chromium (VI): IEC 62321-7-1:2015 (boiling water extraction);
Chromium (VI): IEC 62321-7-2:2017 (solvent and alkaline extraction);
PBBs/PBDEs: IEC 62321-6:2015



Test Conducted 測試內容 :

Remarks 備註:

*1: List of Appropriate Acid 各材質添加酸液如下表 :

Material 材質	Acid Added for Digestion 添加酸液種類
Polymers 聚合物	HNO ₃ ,HCl,HF,H ₂ O ₂ ,H ₃ BO ₃ 硝酸、鹽酸、氫氟酸、雙氧水、硼酸
Metals 金屬	HNO ₃ ,HCl,HF 硝酸、鹽酸、氫氟酸
Electronics 電子產品	HNO ₃ ,HCl,H ₂ O ₂ ,HBF ₄ 硝酸、鹽酸、雙氧水、氟硼酸

*2: If sample solution is significantly more intense than 0.13 µg/cm² equivalent comparison standard, Chromium VI would be determined as detected, the result of visual observation is positive.

當待測樣品溶液顏色明顯比 0.13 µg/cm² 深，採用目測法判定六價鉻結果為陽性。




Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:

Test for Heavy Metal (As,Sb,Be) Contents 重金屬(砷,銻,鉍)

Reference Method 參考方法 : USEPA 3052




Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:

Test for Phthalates Content 鄰苯二甲酸酯測試

Reference Method 參考方法 : IEC 62321-8:2017




Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:

Test for Halogen Content 鹵素測試


Reference Method 參考方法 : EN 14582:2016



Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:

Test for Medium Chain Chlorinated Paraffins (C14~C17) 中鏈氯化石蠟測試流程圖
Reference Method 參考方法 : ISO 18219




Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:

Test for Bisphenol-A Content 雙酚-A 測試


Reference Method 參考方法 : Solvent extraction 溶劑萃取



Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:


Test for Hexabromocyclododecane (HBCDD) 六溴環十二烷測試
Reference Method 參考方法 : USEPA 3540C



Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:

Test for Perfluorooctane Sulfonates (PFOS) / Perfluorooctanoic Acid (PFOA) Content 全氟辛磺酸 / 全氟辛酸測試
Reference Method 參考方法 : CEN/TS 15968:2010




Test Conducted 測試內容 :

Measurement Flowchart 測試流程圖:

Test for TBBPA Content 四溴雙酚-A 測試

Reference Method 參考方法 : USEPA 3540C




Test Conducted 測試內容 :


Measurement Flowchart 測試流程圖:

Test for Polyvinyl Chloride (PVC) 聚氯乙烯測試

Reference Method 參考方法 : Beilstein's Test (Flame Test) / FT-IR Analysis



Sample photo 樣品照片 :



End of Report

Except where explicitly agreed in writing, all work and services performed by Intertek is subject to our standard Terms and Conditions which can be obtained at our website: <http://www.intertek-twn.com/terms/>. Intertek's responsibility and liability are limited to the terms and conditions of the agreement.

This report is made solely on the basis of your instructions and / or information and materials supplied by you and provide no warranty on the tested sample(s) be truly representative of the sample source. The report is not intended to be a recommendation for any particular course of action, you are responsible for acting as you see fit on the basis of the report results. Intertek is under no obligation to refer to or report upon any facts or circumstances which are outside the specific instructions received and accepts no responsibility to any parties whatsoever, following the issue of the report, for any matters arising outside the agreed scope of the works. This report does not discharge or release you from your legal obligations and duties to any other person. You are the only one authorized to permit copying or distribution of this report (and then only in its entirety). Any such third parties to whom this report may be circulated rely on the content of the report solely at their own risk.

Reporting Statements of Conformity: Please note that the test results contain statement of conformity with the decision rules which are based on the specifications of customers, regulations and standards, and does not consider measurement uncertainty.

