TEST REPORT

KOTITI No. | **8226-1401-101756**

Applicant | DUKSAN Hi-Metal **Address** | 66, Muryong 1-ro, Buk-gu, Ulsan, Korea

Date In | Feb 09, 2026 **Date Out** | Feb 23, 2026

Issue No	4750633722
Sample Description	Sn0.7Cu(ULA)
Sample Quantity	One (1) Sample(s)
Buyer	N/S
Item Number	N/S
Material	Metal
Testing Period	Feb 09, 2026 ~ Feb 23, 2026
Test Result	For further details, please refer to the following page(s).

Note:
(1) N/S : Not Submitted
(2) N.A. : Not Applicable
(3) N.D. : Not Detected [< RL(Report Limit)]
(4) Negative : Not Detected, Positive : Detected

Affirmation	Prepared by Name : A Reum Shin	Technical Manager Name : Gun Young Ryu

KOTITI Testing & Research Institute

Contact Information for technical questions and general inquiries.

· Primary Contact : Yun jae Lee **T** (822)3451-7116 **E** yjlee@kr.kotiti-global.com · Back-up : Gun young Ryu **T** (822)3451-7328 **E** gy_ryu@kr.kotiti-global.com

48, Gwacheon-daero 7na-gil, Gwacheon-si, Gyeonggi-do, Republic of Korea **T** (822)6191-6182 **F** (822)3451-7179 **W** www.kotiti-global.com

1. The test results contained in this report are limited to results on the sample(s) that is provided by client and are not necessarily indicative or representative of the qualities of the lot from which the sample(s) was taken or of all products.
2. Further use of the results of this report is prohibited unless allowed under a separate agreement set forth in an official document that is established between the client identified on this letter and the KOTITI Testing & Research Institute.
3. The test result in this report is not related to accreditation of KS Q ISO/IEC 17025 and KOLAS.
4. You can verify the authenticity by the QR code at the bottom right side of the issued report or access http://cs.kotiti-global.com and enter the test report number.

Tested Sample List			
Sample No.	**Sample Description**	**Item No.**	**Material**
1	Sn0.7Cu(ULA)	N/S	Metal

Global Business Partner

Phthalates, Unit : mg/kg
(EU Directive 2011/65/EU, 2015/863/EU)

Test Conducted	Test Method	MDL	Test Results
			1
di(ethylhexyl) phthalate (DEHP)	IEC 62321-8:2017 (Solvent extraction and determined by GC-MS or LC-MS)	50	N.D.
di-n-butyl phthalate (DBP)		50	N.D.
diisobutyl phthalate (DIBP)		50	N.D.
butyl benzyl phthalate (BBP)		50	N.D.


* Tested by : A Reum Shin

Photo of the submitted sample(s)

Sample No.1	

Flow Chart

Phthalates



* The sample is totally digested.