AN14111 Target Wake Time (TWT) on RW61x Rev. 1 – 21 June 2024

Application note

Document information

Information	Content
Keywords	target wake time, wake-up interval, agreement phase, negotiation phase, service period, low- power state, power-down state, active state
Abstract	Describes the target wake time feature and provides examples for RW61x.



1 Overview

IEEE 802.11ax standard supports the target wake time (TWT) feature for 2.4 GHz and 5 GHz. The feature is used to manage the activity of the Wi-Fi stations (STA) and access points (AP) in a basic service set (BSS), where TWT parameter values define how often and for how long a STA is in active state to send and/or receive data.

Compared to the standard power save modes, the power consumption of 802.11ax devices with TWT enabled is significantly reduced. The spectral efficiency is also optimized as there is less contention and overlap between users. TWT is most beneficial for IoT devices such as sensors and actuators.

1.1 Prerequisites

By default, when RW61x is in low-power mode (PM3)¹, the on-chip SRAM is powered down and no data is retained in the memory. To disable the data retention loss in the memory:

- Download the latest SDK from [2].
- Edit *host_sleep.h* file located in *rdrw612bga/wifi_examples/wifi_cli/* directory:
 - Remove the macro #define WLAN_MEM_PD_CFG (1UL << 8)
 - Add the macro #define WLAN MEM PD CFG ((1UL << 8) | 0x3FUL)

Note: 0x3FUL is the value used to change the configuration of the register that controls the SRAM status in PM3 mode.

• Build wifi_cli application from MCUXpresso IDE/ IAR/ ARMGCC/ MDK. Refer to [1].

Note: This change is required to fully utilize and benefit from TWT.

¹ Figure 3 shows a example of RW61x current consumption measurement when the MCU is in low-power mode.

2 Sequence

The sequence of target wake time includes:

- The negotiation phase: the AP and STA(s) negotiate the TWT parameters to access the medium.
- The agreement phase: the AP and STA(s) agree on the TWT parameters and service period (SP).
- The service period (SP): the wake-up duration. Period of time during which the STA must be awake and active.

Figure 1 shows the negotiation phase, agreement phase, wake-up duration/service period in the TWT sequence.



3 TWT parameters

During the negotiation phase, the AP and STA(s) define the following TWT parameter values:

- Explicit/implicit: an AP will/will not send frames in the current service period (SP) to notify a STA of the start of the next SP.
- Announced/unannounced: at the beginning of the SP, a STA will/will NOT send a QoS NULL frame with active mode (PM0) to notify the AP that the STA is awake.
- Trigger/non-trigger: an AP will/will NOT use the OFDMA trigger-based mechanism set in the SP. If the trigger-based mechanism is enabled in the SP, the STA does not send data to the AP until a trigger is received.
- TWT info disabled/enabled: indicates whether TWT information frames are acceptable or not during the TWT session
- Individual/broadcast TWT:
 - Individual TWT (ITWT): initiated by a single STA to determine the wake interval (wake-up duration and start of sleep time)
 - Broadcast TWT (BTWT): scheduled by an AP in its beacon frames. Allows an AP to set up a shared TWT session for a group of STAs and restate the TWT parameters

Note: The RW61x only supports ITWT in STA mode (not BTWT).

- Wake-up duration: period of time during which the STA must be awake and active.
- Flow identifier: up to eight TWT sessions can run in parallel based on a unique 3-bit flow identifier.
- Tweak/Not tweak: if the TWT parameters are not agreed upon, the FW can internally tweak/not tweak the parameters to re-negotiate these.
- Exponent: 1-byte value used to calculate the wake-up interval. See <u>Section 4</u>.
- Mantissa: 1-byte value used to calculate the wake-up interval. See <u>Section 4</u>.
- Request/suggest:
 - Request: the STA requests the TWT parameters from the AP.
 - Suggest: the STA indicates the TWT parameters to the AP.

AN14111

(1)

Target Wake Time (TWT) on RW61x

4 Wake-up interval calculations

The wake- up interval is determined by the target wake time exponent and mantissa (<u>Section 3</u>). The formula is:

 $Wake-up interval = Mantissa \times 2^{Exponent}$

Example:

- Exponent = 0x14 = 20 μs
- 2^20 µs = 1048576 us ~ 1 s
- Mantissa = 0x3c = 60 s
- 60 s/1 s = 60 ticks

For every second (exponent), 60 ticks occur.

5 Commands

Command used to dump, set, and apply the TWT parameters using the Wi-Fi CLI demo application:

wlan-11ax-twt-setup <option> <param_id> <param_data>

Table 1. Command parameters

Parameter	Definition
option	dump = show all TWT parameters set = set a single TWT parameter done = apply the TWT parameters
param_id	Only applicable when option = set Identifier of a parameter 0 = explicit/implicit 1 = unannounced/announced 2 = non-triggered/triggered 3 = enable/disable TWT info 4 = individual/broadcast 5 = wake-up duration 6 = flow identifier 7 = hard constraint (tweak/not tweak) 8 = exponent 9 = mantissa 10 = request/suggest TWT
param_data	Only applicable when option = set 2 byte Hexadecimal data corresponding to the value of the parameter identified by param_id (in bytewise little-endian format)

Example of set exponent command:

wlan-11ax-twt-setup set 8 14

Output example:

```
twt_exponent #### Range: [0-63]
[8]: 0x14
```

Example of set mantissa command:

```
# wlan-11ax-twt-setup set 9 3c 0
```

Output example:

```
twt_mantissa #### Range: [0-65535]
[9]: 0x3c 0x00
```

Example of dump command:

#wlan-11ax-twt-setup dump

Output example:

twt exponent #### Range: [0-63] cfg[twt setup] len[12] param num[11]: implicit ##### 0: TWT session is explicit, 1: Session is implicit [0]: 0x01 announced #### 0: Unannounced, 1: Announced TWT [1]: 0x00 trigger enabled #### 0: Non-Trigger enabled, 1: Trigger enabled TWT [2]: 0x00 twt info disabled ##### 0: TWT info enabled, 1: TWT info disabled [3]: 0x01 negotiation_type #### 0: Individual TWT, 3: Broadcast TWT [4]: 0x00 twt wakeup duration #### time after which the TWT requesting STA can transition to doze state [5]: 0x40 flow identifier #### Range: [0-7] [6]: 0x00 hard constraint #### 0: FW can tweak the TWT setup parameters if it is rejected by AP, 1: FW should not tweak any parameters [7]: 0x01 twt_exponent #### Range: [0-63] [8]: 0x14 twt mantissa #### Range: [0-65535] [9]: 0x39 0x00 twt_request #### Type, 0: REQUEST_TWT, 1: SUGGEST_TWT [10]: 0x00

Example of done command:

#wlan-11ax-twt-setup done

6 Example

The example uses two RW61x boards. One board is brought up as AP and the other board is brought up as STA. Different wake-up intervals are set.

Step 1 – Bring up one RW61x in uAP mode.

```
wlan-set-mac <MAC_address> // set MAC address
wlan-add <profile_name> ssid <ssid> ip:<ip_addr>,<gateway_ip>,<netmask> role uap channel
  <channel> // set the profile name, SSID, IP address, etc
wlan-start-network <profile_name> //start the AP
```

Step 2 – Bring up one RW61x in STA mode and connect the STA to the AP.

```
wlan-set-mac <MAC_address> // set MAC address
wlan-add <profile_name> ssid <ssid> <security> <secret_password> channel <channel> // set
the profile name, SSID, etc of the uAP joining
wlan-connect test // connect to uAP
```

Step 3 – To further reduce the power consumption, enable IEEE power save mode on the STA.

wlan-ieee-ps 1

Step 4 – On the STA, configure TWT parameters.

Commands for 1 min wake-up interval:

```
wlan-11ax-twt-setup set 8 14 // configure exponent to 0x14 wlan-11ax-twt-setup set 9 3c 0 // configure mantissa to 0x003c wlan-11ax-twt-setup done // apply configurations
```

Commands for 5 min wake-up interval:

```
wlan-11ax-twt-setup set 8 14 // configure exponent to 0x14
wlan-11ax-twt-setup set 9 2c 1 // configure mantissa to 0x012c
wlan-11ax-twt-setup done // apply configurations
```

Commands for 10 min wake-up interval:

```
wlan-11ax-twt-setup set 8 14 // configure exponent to 0x14 wlan-11ax-twt-setup set 9 58 2 // configure mantissa to 0x0258 wlan-11ax-twt-setup done // apply configurations
```

Step 5 – To maximize the power save, enable the low-power mode (PM3) on the host side of RW61x (Cortex-M33), and enable TWT on the controller/wireless radio side of RW61x.

```
wlan-host-sleep 1 manual
wlan-suspend 3
```

Command output example:

Enter low power mode PM3

7 TWT current consumption measurements

Table 2 includes RW61x current consumption values measured on VBAT pins at different wake-up intervals.

Table 2. RW61x current consumption values measured on VBAT pin

Conditions	Wake-up interval	BGA package [1]	QFN package [1]	Unit
MCU in sleep mode (PM3)	1 min	280	285	μA
Wi-Fi subsystem in low power mode	5 min	240	250	μA
Narrowband subsystem in power down mode	10 min	230	240	μA
	20 min	225	235	μA
	30 min	220	230	μA

[1] 0 KB memory retention

8 Appendix

Figure 2 shows the measurement of RW61x current consumption with the MCU (Cortex-M33) in active mode (PM0).



Target Wake Time (TWT) on RW61x



Figure 3 shows the measurement of RW61x current consumption with the MCU (Cortex-M33) in sleep mode (PM3).

Figure 3. Measurement of RW61x current consumption - MCU in sleep mode (PM3)

9 Abbreviations

Table 3. Abbreviations				
Acronym	Description			
AP	Access point			
BSS	Basic service set			
BTWT	Broadcast TWT			
ITWT	Individual TWT			
QoS	Quality of service			
SP	Service period			
STA	Station			
тwт	Target wake time			

10 References

- [1] User manual UM11799 NXP Wi-Fi and Bluetooth Demo Applications for RW61x
- [2] Web page Select board | MCUXpresso SDK builder (<u>link</u>)

11 Note about the source code in the document

The example code shown in this document has the following copyright and BSD-3-Clause license:

Copyright 2024 NXP Redistribution and use in source and binary forms, with or without modification, are permitted provided that the following conditions are met:

- 1. Redistributions of source code must retain the above copyright notice, this list of conditions and the following disclaimer.
- 2. Redistributions in binary form must reproduce the above copyright notice, this list of conditions and the following disclaimer in the documentation and/or other materials must be provided with the distribution.
- 3. Neither the name of the copyright holder nor the names of its contributors may be used to endorse or promote products derived from this software without specific prior written permission.

THIS SOFTWARE IS PROVIDED BY THE COPYRIGHT HOLDERS AND CONTRIBUTORS "AS IS" AND ANY EXPRESS OR IMPLIED WARRANTIES, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE ARE DISCLAIMED. IN NO EVENT SHALL THE COPYRIGHT HOLDER OR CONTRIBUTORS BE LIABLE FOR ANY DIRECT, INDIRECT, INCIDENTAL, SPECIAL, EXEMPLARY, OR CONSEQUENTIAL DAMAGES (INCLUDING, BUT NOT LIMITED TO, PROCUREMENT OF SUBSTITUTE GOODS OR SERVICES; LOSS OF USE, DATA, OR PROFITS; OR BUSINESS INTERRUPTION) HOWEVER CAUSED AND ON ANY THEORY OF LIABILITY, WHETHER IN CONTRACT, STRICT LIABILITY, OR TORT (INCLUDING NEGLIGENCE OR OTHERWISE) ARISING IN ANY WAY OUT OF THE USE OF THIS SOFTWARE, EVEN IF ADVISED OF THE POSSIBILITY OF SUCH DAMAGE.

AN14111

12 Revision history

Table 4.	Revision	history

Document ID	Release date	Description
AN14111 v.1.0	21 June 2024	Initial version

Target Wake Time (TWT) on RW61x

Legal information

Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at https://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this document expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at <u>PSIRT@nxp.com</u>) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

 $\ensuremath{\mathsf{NXP}}\xspace \mathsf{B.V.}\xspace \longrightarrow$ NXP B.V. is not an operating company and it does not distribute or sell products.

Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

Bluetooth — the Bluetooth wordmark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by NXP Semiconductors is under license.

Target Wake Time (TWT) on RW61x

Tables

Tab. 1.	Command parameters6
Tab. 2.	RW61x current consumption values
	measured on VBAT pin9

Tab. 3.	Abbreviations	12
Tab. 4.	Revision history	15

Figures

Fig.	1.	TWT	sequence		3
	~			C	

- Fig. 2. Measurement of RW61x current consumption MCU in active mode (PM0) 10
- Fig. 3. Measurement of RW61x current consumption MCU in sleep mode (PM3)11

Target Wake Time (TWT) on RW61x

Contents

1	Overview	2
1.1	Prerequisites	2
2	Sequence	3
3	TWT parameters	4
4	Wake-up interval calculations	5
5	Commands	6
6	Example	8
7	TWT current consumption	
	measurements	9
8	Appendix	10
9	Abbreviations	12
10	References	13
11	Note about the source code in the	
	document	14
12	Revision history	15
	Legal information	16

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© 2024 NXP B.V.

All rights reserved.

For more information, please visit: https://www.nxp.com

Document feedback Date of release: 21 June 2024 Document identifier: AN14111